

Developmental Technical Data Guide

Chem Link Inc.

Telephone: 800-826-1681 Fax: 269-679-4448
353 East Lyons
Schoolcraft, MI 49087
www.chemlinkinc.com

Last Revision: 04/29/10

Product Description

Chem Link **SOF®-Rod** is a cylindrical, flexible foam rod for use as a sealant backing. **SOF®-Rod** is composed of a bi-cellular material, TYPE B, as defined in ASTM C 1330. **SOF®-Rod** may also be used as a gasket or sealing material as per ASTM C 717.

Application Instructions

Common applications include, but are not limited to, expansion and contraction joints, window glazing, curtain wall construction partitions, parking decks, bridge construction, modular home gasketing, and log home chinking.

Benefits

Use of **SOF®-Rod** limits the depth of the sealant and prevents excessive sealant use. It also acts as a barrier to the flow of sealant through the joint, helps prevent 3 point bonding, and forces the sealant to take a more optimum shape prolonging sealant service life.

Joint Preparation / Installation

Just prior to placing **SOF®-Rod**, clean all joints per the sealant manufacturer's recommendations. Thoroughly remove any concrete form-release agents, curing compound residue, laitance, or any foreign materials. To ensure a good sealant bond, joints must be clean, dry, and free of contamination prior to sealant application. Air compressors used for this purpose must be equipped with traps for removal of oil and moisture. Install the backer rod at the depth recommended on the corresponding sealant data guide.

Advantages

- Easy to apply
- No outgassing
- Chemically inert
- Virtually dust-free
- Non-absorbent

Compatibility

SOF®-Rod is composed of a bi-cellular polyolefin foam. Bi-cellular polyolefin foam is compatible, both physically and chemically, with most cold applied sealants. Compatibility of sealants in contact with backings can be evaluated according to ASTM 1087 test Method C.

Size Selection

Proper size selection is important as it controls the depth of the sealant bead and helps prevent three point bonding. Chem Link recommends the backer rod be oversized (25-50%) and fit tightly into the joint to function as a bond breaker.

Precautions:

Do not puncture, over compress or stretch backer rod during insertion. Do not use with hot applied sealants. Test for outgassing of cold applied sealants in accordance with ASTM Test Method C 1253. Sealant compatibility should be confirmed by the sealant manufacturer.

TEMPERATURE LIMITS: -45°F (-42°C) to +160°F (71°C.)

IMPORTANT NOTICE

Except where prohibited by law, Chem Link makes no warranties, expressed or implied, statutory or otherwise, including but not limited to, any implied condition or warranty of merchantability or fitness for a particular purpose. User is responsible for determining whether this Chem Link product is fit for a particular purpose and suitable for user's method of application.

LIMITATIONS OF REMEDIES AND LIABILITY

If this Chem Link product is proved to be defective, the exclusive remedy at Chem Link's option shall be to refund the purchase price of or to repair or replace the defective Chem Link product. Chem Link shall not otherwise be liable for loss of damages, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including negligence, warranty or strict liability.

SOF® is a registered trade mark of Nomaco, Inc.

